



**Shaanxi Huatainuo
Metal Co., Ltd.**

Titanium has unlimited potential.
Based on quality and innovation, we look forward
to working with you to create brilliance in various fields.

Shaanxi Huatainuo Metal Co., Ltd.

Add: No. 21 Changsheng Road, Gaoxin Avenue,
High tech Development Zone, Baoji City,
Shaanxi Province

Tel: +86 181 4917 6746

Email: elsa.sales@htn-ti.com

Web: www.htn-ti.com



 LinkedIn



 Facebook



 WhatsApp

Innovation Forged in Titanium Shaping the Future of Industry.

We don't just supply titanium
we engineer solutions that push material boundaries

Company Profile

Shaanxi Huatainuo Metal Co., Ltd. specializes in the research, development, and manufacturing of high-performance titanium materials. Our product portfolio includes titanium rods, wires, powders, plates, and precision-machined components. Engineered with advanced production technologies and strict quality control systems, our titanium products deliver exceptional corrosion resistance and mechanical strength.

They are widely trusted in aerospace, medical implants, chemical equipment, and marine engineering applications. With reliable delivery capability and a multilingual international service team, Huatainuo has established itself as a trusted partner for clients worldwide.

CORE COMPETENCIES

Medical-Grade Titanium Products

- ◆ Implant-quality Ti-6Al-4V ELI bars/wires (ASTM F136)
- ◆ Custom surface treatments (sandblasted, acid-etched) for enhanced bio-compatibility
- ◆ Traceable materials for surgical implants, dental components, and orthopedic devices

Industrial-Grade Reliability

- ◆ Aerospace: Lightweight CP-Ti Grade 1-4 bars/wires (ASTM B348) for aerospace and chemical processing.
- ◆ Marine and Automotive: High-strength Ti-3Al-2.5V bars/wires (ASTM B348) for marine and automotive applications requiring corrosion resistance and durability.
- ◆ Chemical Processing: Corrosion-resistant rods for heat exchangers.
- ◆ Consumer Electronics: Precision-drawn wires for smart device components.

Manufacturing Excellence

- ◆ Vertical Integration: Full-process control from titanium sponge to finished product
- ◆ Advanced Equipment: VAR melting, precision rolling, and cold-drawing technologies
- ◆ Quality Assurance: In-house lab with testing for tensile strength & fatigue resistance and micro-structure analysis

Qualifications and Honors



Medical Titanium Rod

Medical titanium rod is a high-strength, bio-compatible titanium alloy bar used primarily in orthopedic and trauma implants, such as spinal fixation rods, intramedullary nails, and bone pins.

Highly elastic medical titanium wire High Strength medical titanium wire

Grade: TC4,TC20,Gr5,Ti-6Al-4V,Ti-6Al-4V ELI,Ti-6Al-7Nb

Standard: GB/T 13810, ASTM F136, ISO 5832-3, ASTM F1295, ISO 5832-11

Size(mm): $\varnothing 0.8, \varnothing 1.0, \varnothing 1.2, \varnothing 2.0, \varnothing 3.0, \varnothing 4.0$

Characteristic: Surface roughness $\leq 0.4\mu\text{m}$, suitable for Kirschner wire, elastic intramedullary nail, etc. The strength of these wires can reach 1200MPa.




Titanium bar for bone screw

Grade: TC4,TC20,Gr5,Ti-6Al-4V,Ti-6Al-4V ELI,Ti-6Al-7Nb

Standard: GB/T 13810, ASTM F136, ISO 5832-3, ASTM F1295, ISO 5832-11

Size(mm): $\varnothing 4, \varnothing 6, \varnothing 8, \varnothing 10, \varnothing 12$

Characteristic: 1、The physical properties of materials are controllable and customized. 2、The macrostructure and microstructure of the material can be controlled and customized. 3、Suitable for cortical bone screws, cancellous bone screws, locking screws, medical titanium rods.



Titanium bar for spine screws

Grade: TC4,TC20,Gr5,Ti-6Al-4V,Ti-6Al-4V ELI,Ti-6Al-7Nb

Standard: GB/T 13810, ASTM F136, ISO 5832-3, ASTM F1295, ISO 5832-11

Size(mm): $\varnothing 10, \varnothing 13, \varnothing 14, \varnothing 14.2, \varnothing 14.5$

Characteristic: Shrinkage $\leq 0.03\text{mm}$, and the metallography can be controlled.



Medical Titanium Rod

■ Titanium bar for dental implants

Grade: TA3,TA4,TC4,TC20,Gr3,Gr4,Gr5,GD4B,
Ti-6Al-4V, Ti-6Al-4V ELI, Ti-6Al-7Nb

Standard: GB/T 13810, ASTM F67, ISO 5832-2,
ASTM F136, ISO 5832-3, ASTM F1295, ISO 5832-11

Size(mm): Ø3.0,Ø4.0,Ø6.0,Ø10.0,Ø90,Ø100

Characteristic: Consistency of physical properties
is good, and the high tolerance precision of bar and
wire reach h6/h7/h8




■ Titanium bar for hip joint

Grade: TA3,TC4,TC20,Gr3,Gr5,Ti-6Al-4V,Ti-6Al-4V ELI,Ti-6Al-7Nb

Standard: GB/T 13810, ASTM F67, ISO 5832-2, ASTM F136, ISO 5832-3, ASTM F1295, ISO 5832-11

Size(mm): Ø16,Ø17.2,Ø18,Ø20,Ø24,Ø30,Ø40,Ø45,Ø50,Ø55,Ø65

Characteristic: Strong plasticity, controllable macrostructure and customizable
physical properties



■ Surgical instrument blanks (scissors, pliers)

Grade: Gr5

Standard: ASTM F136

Size(mm): Ø18,Ø15

Characteristic: High strength, lightweight, resistant to repeated disinfection and corrosion,
anti fatigue, can be processed into high-end reusable surgical instruments.





Product Advantages

Comparison of Huatainuo Titanium Rod with Similar Products from Foreign Competitors

Table 1: Chemical Composition Comparison of Titanium Rod for Surgical Implants

Serial number	Orginal	Grade	Size	Al	V	Fe	C	N	H	O
1	HuatainuoTitanium	TC4	14mm	5.95	4.06	0.187	0.019	0.017	0.003	0.11
2	HuatainuoTitanium	TC4	10mm	6.01	4.10	0.169	0.016	0.019	0.001	0.09
3	HuatainuoTitanium	TC4	6.0mm	6.06	3.94	0.115	0.015	0.024	0.001	0.09
4	HuatainuoTitanium	TC4ELI	14.5mm	6.27	4.23	0.152	0.014	0.025	0.001	0.13
5	US	Ti-6Al-4V	14mm	6.07	4.06	0.104	0.029	0.013	0.002	0.12
6	US	Ti-6Al-4V	6.0mm	6.41	3.72	0.085	0.021	0.03	0.006	0.15
7	US	Ti-6Al-4VELI	10mm	5.93	3.97	0.122	0.02	0.012	0.002	0.12
8	US	Ti-6Al-4VELI	6.0mm	5.94	4.02	0.168	0.015	0.008	0.002	0.10
9	TW	Ti-6Al-4V	13mm	6.04	4.05	0.171	0.007	0.009	0.005	0.10
10	Ru	Ti-6Al-4V	6.0mm	5.69	4.08	0.290	0.038	0.008	0.008	0.11

Table 1 shows:

All chemical compositions meet the standard requirement GB/T 3620.1, but for Huatainuo No.1,2,3, US No.5 & TW No.9, the chemical composition can reach the TC4 ELI. It shows the requirement for ELI and the control of the impurity has reach the high level.

Table 2: Comparison of Mechanical Properties of Titanium Bars for Surgical Implants

Serial number	Orginal	Grade	Size	Tensile strength MPa	Yield strength MPa	Elonga tion	Reductio n of area	Metallographic
1	HuatainuoTitanium	TC4	14mm	1052	941	17	54	A1
2	HuatainuoTitanium	TC4	10mm	1041	994	16.5	52	A1
3	Huatainuo Titanium	TC4	6.0mm	1002	895	16.4	54	A1
4	HuatainuoTitanium	TC4ELI	14.5mm	1081	1001	15.5	46	A1
5	US	Ti-6Al-4V	14mm	1002	953	17.5	54	A1
6	US	Ti-6Al-4V	6.0mm	959	842	17	44	A1
7	US	Ti-6Al-4VELI	10mm	1060	915	15	54	A1
8	US	Ti-6Al-4VELI	6.0mm	980	855	14	32	A1
9	TW	Ti-6Al-4V	13mm	1060	995	18	45	A1
10	Ru	Ti-6Al-4V	6.0mm	1094	923	16.5	51	A1

Table 2 shows:

All mechanical properties meet and exceed the standard requirements GB/T13810, but the tensile strength of Huatainuo is relatively concentrated and better uniformity.

Product Control Procedure

Autonomous control program

The company's production process control capability								
Rod/wire								
Rod/wire	Electrode Pressing	Ingot Melting	Ingot Forging	Blank Rolling	Finished Product Drawing	Straightening Annealing/Grinding	Annealing	Finished Product Inspection
Control Status	Automatic Control	Automatic Control	Automatic Control	Automatic Control	Automatic Control	Automatic Control	Automatic Control	Automatic Control
Plate								
Rod/wire	Electrode Pressing	Smelting	Ingot Forging	Blank Rolling	Finished Product Drawing	Finished Product Precision Rolling	Finished Product Inspection	
Control Status	Automatic Control	Automatic Control	Automatic Control	Subcontracted	Automatic Control	Automatic Control	Automatic Control	

Inspection control process

The company's production process control capability						
Finished Product Inspection Items for Bars/Wires	Straightness	Ferrule Inspection	Dimension Inspection	Ultrasonic Flaw Detection	Eddy Current Detection	Surface Inspection
GB/T13810 - 2017	100%	None	100%	> 7.0mm, 100% flaw detection	None	100%
Shaanxi Huatainuo Metal	Platform inspection	100% ferrule passed inspection	100% laser diameter measurement	≥ 6.0mm, 100% manual/four - channel automatic flaw detection	≤ 10.0mm, 100% eddy current detection	100% optical inspection + manual inspection

Table 3: Comparison of Straightness, Dimensional Deviation, Surface, and Necking Test of Titanium Bars for Surgical Implants

Serial number	Orginal	Grade	Size	Bend test (mm/m)	Diameter tolerance (mm)	Shrinkage test	
						1	2
1	HuatainuoTitanium	TC4	14mm	0.3	0, -0.027	-0.03	-0.03
2	Huatainuo Titanium	TC4	10mm	0.25	0, -0.022	/	/
3	HuatainuoTitanium	TC4	6.0mm	0.2-0.25	0, -0.018	/	/
4	HuatainuoTitanium	TC4ELI	14.5mm	0.23	0, -0.020	-0.03	-0.03
5	US	Ti-6Al-4V	14mm	0.20	0, -0.02	-0.05	-0.06
6	US	Ti-6Al-4V	6.0mm	0.23	0, -0.024	/	/
7	US	Ti-6Al-4VELI	10mm	0.21	0, -0.03	/	/
8	US	Ti-6Al-4VELI	6.0mm	0.22	0, -0.023	/	/
9	TW	Ti-6Al-4V	13mm	0.25	0, -0.03	-0.04	-0.05
10	Ru	Ti-6Al-4V	6.0mm	0.20	0, -0.02	/	/

Table 3 shows:

The diameter deviation and external quality of the ten groups of sample rods are controlled at the same level.For high-precision medical small -mouth products, Huatainuo unique production process can control the shrinkage of the products within 0.03mm.

Remark:

The above data shows that Huatainuo titanium bars’ quality is equal to that of those from America, Taiwan (China) and Russia, but with more stable quality and more attractive price.

Production Equipment



■ ALD vacuum melting furnace imported from Germany ■ 4500T hydraulic machine



■ Vacuum annealing oven ■ Polishing machine ■ 25MN fast hydraulic forging machine




■ Grinding machine ■ Precision Wire Mill ■ Cold Rolling Mill

Inspection Equipment



■ Microcomputer control electronic universal testing machine ■ Infra-ray diameter gauge ■ ODE optical surface detector



■ Eddy current flaw detector ■ Automatic Rotating Head Ultrasonic Flaw-detecting Machine

Spot Inventory



Huatainuo's Strategic Objective

Strategic Goals

1. Global Expansion – Strengthen our presence in Europe, North America, and Southeast Asia through local partnerships, international trade fairs, and digital marketing.
2. Technology Leadership – Continuously invest in advanced titanium processing and R\&D to meet the demanding requirements of aerospace, medical, and renewable energy sectors.
3. Quality Excellence – Ensure compliance with ASTM, ISO, and CE standards, supported by robust in-house testing and third-party certifications.
4. Customer Partnership – Provide tailored solutions, fast response, and reliable delivery, supported by multilingual teams for seamless global communication.
5. Sustainability – Commit to eco-friendly production practices and actively explore additive manufacturing and clean energy applications for long-term growth.

Global Business: Centered on product quality and professional technical support, we adhere to international standards and collaborate with global industry partners to deliver traceable, reliable titanium solutions for aerospace, medical, energy and other critical sectors—continuously strengthening our global brand recognition.

